



Eaton B118-002-UHD-2

B118-002-UHD-2-PDH

□□□□

PRODUCT NAME	Eaton Tripp Lite series splitter
CATALOG NUMBER	B118-002-UHD-2
UPC	037332200648
PRODUCT LENGTH/DEPTH	7.24 in
PRODUCT HEIGHT	2.16 in
PRODUCT WIDTH	6.45 in
PRODUCT WEIGHT	0.187 lb
WARRANTY	3 year limited
COMPLIANCES	RoHS WEEE Directive FCC Compliant CE Marked REACH
CERTIFICATIONS	NOM

TYPE	Splitter
AUDIO SPECIFICATION	DTS-HD, Dolby TrueHD, Dolby Digital Plus and LPCM 7.1 Channel Surround Sound
DEVICE COMPATIBILITY	Monitor/HDTV
AC POWER ADAPTER PLUG(S)	NEMA 5-15P North America BS 1363 UK CEE 7/16 Schuko AS/NZS 3112 Australia
RELATIVE HUMIDITY	0-85% non-condensing
COLOR	Black
MATERIAL	Metal
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	Video
PRODUCT FEATURES	HDR Support TAA Compliant EDID Compatible Rackmountable Daisy-chainable / Cascadable 3D Video Supported
COLOR DEPTH	36-bit Deep color 36-bit Deep Color
PACKAGE CONTENTS	Mounting hardware B118-002-UHD-2 2-Port 4K 3D HDMI Splitter External power supply (Input: 100–240V, 50/60 Hz, 0.35A; Output: 5V 2A) Owner’s manual International plug adapters (North America, Europe, U.K. and Australia)
PRODUCT HIGHLIGHTS	Distributes A/V up to 15 ft. when used with 28 AWG HDMI cable Supports UHD resolutions up to 4K @ 60 Hz (3840 x 2160) for crystal-clear video Expand the number of connected displays, up to 32, by cascading up to 3 levels of splitters together Plug-and-play operation with no software required for easy, immediate installation 3-year limited warranty (Worldwide) Supports High Dynamic

	Range (HDR) for richer contrast and expanded color accuracy
PACKAGING TYPE	Box
POWER SOURCE TYPE	AC Adapter
HDCP SPECIFICATION	2.2
SIDEA CONNECTOR1	HDMI (FEMALE)
SIDEB CONNECTOR1	HDMI (FEMALE)
DC BARREL PLUG	OD: 5.5 x 2.1 x 7.5 mm, positive pin, negative sleeve
SIDEB CONNECTOR3	HDMI (FEMALE)
VOLTAGE COMPATIBILITY (VAC)	100 VAC
	110 VAC
	120 VAC
	125 VAC
	127 VAC
	200 VAC
	208 VAC
	220 VAC
	230 VAC
	240
HOST CONNECTOR	HDMI (FEMALE)
TECHNOLOGY	HDMI
FEATURES	Flex Center
CONNECTOR GROUP	HDMI
CONNECTOR	HDMI (female)
AC POWER ADAPTER CORD LENGTH	4 ft
AC ADAPTER	Input: 100-240V, 50/60Hz, 0.35A; Output: 5V, 2A, 4 ft
INCLUDED MOUNTING ACCESSORIES	Yes
MAX SUPPORTED VIDEO RESOLUTION	3840 x 2160 (4K) @ 60Hz
MOUNTING DETAILS	Yes
LED INDICATORS	(x1) Green (Power), (x2) Orange (Signal)
OPERATING TEMPERATURE RANGE	32° to 104°F (0° to 40°C)
STORAGE TEMPERATURE RANGE	5° to 122°F (-15° to 50°C)
NUMBER OF PORTS	2
MAX RESOLUTION	4K/60
TAA COMPLIANCE	Yes
INPUT X OUTPUT	1 x 2

