



Eaton B118-004-UHD-2

4-Port HDMI Splitter - 4K @ 60 Hz, HDCP 2.2, HDR, TAA

□□□□

PRODUCT NAME	Eaton Tripp Lite series splitter
CATALOG NUMBER	B118-004-UHD-2
UPC	037332200655
PRODUCT LENGTH/DEPTH	3.97 in
PRODUCT HEIGHT	1.17 in
PRODUCT WIDTH	5.04 in
PRODUCT WEIGHT	0.198 lb
WARRANTY	3 year limited
COMPLIANCES	FCC Compliant RoHS CE Marked

□□□□	
TYPE	Splitter
AUDIO SPECIFICATION	DTS-HD, Dolby TrueHD, Dolby Digital Plus and LPCM 7.1 Channel Surround Sound
DEVICE COMPATIBILITY	Monitor/HDTV
AC POWER ADAPTER PLUG(S)	CEE 7/16 Schuko AS/NZS 3112 Australia NEMA 5-15P North America BS 1363 UK
RELATIVE HUMIDITY	0-85% non-condensing
COLOR	Black
MATERIAL	Metal
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	Video
PRODUCT FEATURES	Daisy-chainable / Cascadable TAA Compliant Rackmountable 3D Video Supported EDID Compatible HDR Support
COLOR DEPTH	36-bit Deep color 36-bit Deep Color
PACKAGE CONTENTS	External power supply (Input: 100–240V, 50/60 Hz, 0.35A; Output: 5V 2A) Mounting hardware Owner’s manual B118-004-UHD-2 4-Port 4K 3D HDMI Splitter International plug adapters (North America, Europe, U.K. and Australia)
PRODUCT HIGHLIGHTS	Plug-and-play operation with no software required for easy, immediate installation Distributes A/V up to 15 ft. when used with 28 AWG HDMI cable Supports UHD resolutions up to 4K @ 60 Hz for crystal-clear video Carries High Dynamic Range (HDR) signals for rich contrast and expanded color accuracy Expand the number of connected displays, up to 64, by cascading up to 3 levels

	3-year limited warranty (Worldwide)
PACKAGING TYPE	Box
POWER SOURCE TYPE	AC Adapter
HDCP SPECIFICATION	2.2
SIDEA CONNECTOR1	HDMI (FEMALE)
SIDEB CONNECTOR1	HDMI (FEMALE)
DC BARREL PLUG	OD: 5.5 x 2.1 x 7.5 mm, positive pin, negative sleeve
SIDEB CONNECTOR3	HDMI (FEMALE)
VOLTAGE COMPATIBILITY (VAC)	100 VAC 110 VAC 120 VAC 125 VAC 127 VAC 200 VAC 208 VAC 220 VAC 230 VAC 240
HOST CONNECTOR	HDMI (FEMALE)
TECHNOLOGY	HDMI
FEATURES	Flex Center
CONNECTOR GROUP	HDMI
CONNECTOR	HDMI (female)
AC POWER ADAPTER CORD LENGTH	4 ft
AC ADAPTER	Input: 100-240V, 50/60Hz, 0.35A; Output: 5V, 2A, 4 ft
INCLUDED MOUNTING ACCESSORIES	Yes
MAX SUPPORTED VIDEO RESOLUTION	3840 x 2160 (4K) @ 60Hz
MOUNTING DETAILS	Yes
LED INDICATORS	Green (Power), (x2) Orange (Signal)
OPERATING TEMPERATURE RANGE	32° to 104°F (0° to 40°C)
STORAGE TEMPERATURE RANGE	5° to 122°F (-15° to 50°C)
NUMBER OF PORTS	4
MAX RESOLUTION	4K/60
TAA COMPLIANCE	Yes
INPUT X OUTPUT	1 x 4

