



Eaton B122-000

HDMI Signal Booster / Extender, 1920 x 1200 (1080p) 24Hz, Up to 150 ft. (45 m), (HDMI F/F),TAA

□□□□

PRODUCT NAME	Eaton Tripp Lite series signal booster
CATALOG NUMBER	B122-000
UPC	037332133144
PRODUCT LENGTH/DEPTH	1.02 in
PRODUCT HEIGHT	2.36 in
PRODUCT WIDTH	0.6 in
PRODUCT WEIGHT	0.03 lb
WARRANTY	3 year limited
COMPLIANCES	RoHS FCC Compliant REACH CE Marked

□□□□	
TYPE	Signal Booster
AUDIO SPECIFICATION	Pass-through audio
AUDIO PORTS	HDMI (FEMALE) HDMI (Female) port allows for pass-through audio
RELATIVE HUMIDITY	0-85% non-condensing
AUDIO INPUT	HDMI
COLOR	Black
AUDIO OUTPUT	HDMI
INPUT	Unit (optional)
MATERIAL	Plastic (PC)
CONNECTOR TYPE	Video
PRODUCT FEATURES	EDID Compatible TAA Compliant 3D Video Supported Consumer Electronics Control (CEC) Supported
COLOR DEPTH	24-bit True color 24-bit True Color
PACKAGE CONTENTS	B122-000 HDMI Signal Extender Owner's Manual
PRODUCT HIGHLIGHTS	3-year limited warranty (Worldwide) A 3D signal can be extended up to 125-ft. (38.1 m) using 24Awg HDMI cable Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases 24Awg HDMI cable is also needed when extending a 3D signal more than 50-ft. (15.24 m). No external power required in most installations Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound Audio Extend a 1080p @ 24Hz (or 1920 x 1200) HDMI signal up to 150-ft. (45.72 m) from the source When extending a 1080p @ 24Hz (or 1920 x 1200) signal more than 75-ft. (22.86 m), use cable made with 24Awg wiring, such as the P568-100-HD

□□

PACKAGING TYPE	Box
CHROMA SUB SAMPLING	4:4:4
POWER SOURCE TYPE	USB
HDCP SPECIFICATION	1.4
SIDEA CONNECTOR1	HDMI (FEMALE)
SIDEB CONNECTOR1	HDMI (FEMALE) MICRO-USB B (FEMALE)
SIDEA CONNECTOR2	MICRO-USB B (FEMALE)
SIDEB CONNECTOR3	HDMI (FEMALE)
POWER SOURCE	Unit (optional)
TECHNOLOGY	HDMI
FEATURES	Flex Center
VIDEO PORTS DETAILS	• HDMI 1.4 • HDCP 1.4
CONNECTOR GROUP	HDMI
CONNECTOR	HDMI (female)
NUMBER OF DISPLAYS	1
NUMBER OF MONITORS SUPPORTED	1
INCLUDED MOUNTING ACCESSORIES	No
HOUSING	Plastic
MAX SUPPORTED VIDEO RESOLUTION	1920 x 1200 @ 24Hz
MOUNTING DETAILS	No
OPERATING TEMPERATURE RANGE	32° to 104°F (0° to 40°C)
RESOLUTIONS SUPPORTED	1920 x 1200 (1080p) @ 24Hz, up to 150 ft.
STORAGE TEMPERATURE RANGE	5° to 122°F (-15° to 50°C)
VIDEO INPUT	HDMI (FEMALE)
VIDEO OUTPUT	HDMI (FEMALE)
MAX 1024 X 768 RANGE (FT)	150 ft
MAX 1080I RANGE (FT)	150 ft
MAX 1080P RANGE (FT)	150 ft
MAX 1440 X 900 RANGE (FT)	150 ft
MAX 1600 X 1200 RANGE (FT)	150 ft
MAX 480I RANGE (FT)	153 ft
MAX 480P RANGE (FT)	153 ft
MAX 640 X 480 RANGE (FT)	150 ft

MAX 720P RANGE (FT)	150 ft
MAX 800 X 600 RANGE (FT)	150 ft
VIDEO PORTS	HDMI (FEMALE)
NUMBER OF PORTS	1
MAX RESOLUTION	1080p
EXTENDER STYLE	Box
EXTENSION METHOD	HDMI Cable
TAA COMPLIANCE	Yes
FORM FACTOR/MOUNTING OPTIONS	Box

□□□□:	
□□□□:	
□□□:	
□□:	