



Eaton B3205-5/8X7 1/2HDG

Eaton B-Line series all threaded rod, 0.5" H x 0.5" D, Steel, 1692 Lbs load cap, 5/8"-11 thread/rod size, 2.5" thread length, 750 op temp

□□□□

PRODUCT NAME	Eaton B-Line series all threaded rod
CATALOG NUMBER	B3205-5/8X7 1/2HDG
UPC	799038737117
PRODUCT LENGTH/DEPTH	7.5 in
PRODUCT HEIGHT	0.625 in
PRODUCT WIDTH	0.625 in
PRODUCT WEIGHT	0.33 lb
CERTIFICATIONS	Not Applicable

Application	
OPERATING TEMPERATURE - MAX	750 °F

Load rating/capacity	
LOAD CAPACITY	1692 lb

Model	
THREAD LENGTH	2.5 in
THREAD/ROD SIZE	5/8"-11
TYPE	Threaded rod with (right & left hand threads)

Material/finish	
MATERIAL	Steel
