

Eaton BAB2015

Eaton BAB thermal magnetic circuit breaker, Quicklag industrial thermal-magnetic circuit breaker, Bolt-on mounting, Switching neutral, 15 A, 10 kAIC, Two-pole, 120/240 V, Non-Interchangeable, Q7, BAB

PRODUCT NAME	Eaton BAB thermal magnetic circuit breaker
CATALOG NUMBER	BAB2015
UPC	786679302156
PRODUCT LENGTH/DEPTH	3.8 in
PRODUCT HEIGHT	4.8 in
PRODUCT WIDTH	2.1 in
PRODUCT WEIGHT	0.65 lb
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	HACR rated

AMPERAGE RATING	15 A
VOLTAGE RATING	120/240 V
TRIP TYPE	Non-Interchangeable
CIRCUIT BREAKER TYPE	BAB
INTERRUPT RATING	10 kAIC
NUMBER OF POLES	Two-pole
QUANTITY	7
TYPE	Quicklag Industrial Circuit Breaker

SPECIAL FEATURES

- Bolt-on mounting
- Switching neutral
- TORQUE 4-10 AWG 20 IN LBS
- 8AWG 25 IN LBS
- 6-4 AWG 27 IN LBS

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

