

Eaton BAB2020

Eaton BAB thermal magnetic circuit breaker, Quicklag industrial thermal-magnetic circuit breaker, Bolt-on mounting, Switching neutral, 20 A, 10 kAIC, Two-pole, 120/240 V, Non-Interchangeable, Q7, BAB

PRODUCT NAME	Eaton BAB thermal magnetic circuit breaker
CATALOG NUMBER	BAB2020
UPC	786679302200
PRODUCT LENGTH/DEPTH	2.906 in
PRODUCT HEIGHT	2.906 in
PRODUCT WIDTH	2 in
PRODUCT WEIGHT	0.55 lb
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	HACR rated

AMPERAGE RATING	20 A
VOLTAGE RATING	120/240 V
TRIP TYPE	Non-Interchangeable
CIRCUIT BREAKER TYPE	BAB
INTERRUPT RATING	10 kAIC
NUMBER OF POLES	Two-pole
QUANTITY	7
TYPE	Quicklag industrial thermal-magnetic circuit breaker
SPECIAL FEATURES	• Bolt-on mounting • Switching neutral

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

