

Eaton BAB2030

Eaton BAB thermal magnetic circuit breaker, Quicklag industrial thermal-magnetic circuit breaker, Switching neutral, 30 A, 10 kAIC, Two-pole, 120/240 V, Non-Interchangeable, Q7, BAB, Ring or spade lug terminals

PRODUCT NAME	Eaton BAB thermal magnetic circuit breaker
CATALOG NUMBER	BAB2030
UPC	786679302309
PRODUCT LENGTH/DEPTH	3.9 in
PRODUCT HEIGHT	4.8 in
PRODUCT WIDTH	2.2 in
PRODUCT WEIGHT	0.55 lb
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	HACR rated

AMPERAGE RATING	30 A
VOLTAGE RATING	240 V - 240 V
TRIP TYPE	Non-Interchangeable
CIRCUIT BREAKER TYPE	BAB
TERMINALS	Ring or spade lug
INTERRUPT RATING	10 kAIC
NUMBER OF POLES	Two-pole
QUANTITY	7
TYPE	Quicklag industrial thermal-magnetic circuit breaker
SPECIAL FEATURES	Switching neutral

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

