

Eaton BAB2050

Eaton BAB thermal magnetic circuit breaker, Quicklag industrial thermal-magnetic circuit breaker, Bolt-on mounting, High intensity discharge, 50 A, 10 kAIC, Two-pole, 120/240 V, Non-Interchangeable, Q7, BAB

PRODUCT NAME	Eaton BAB thermal magnetic circuit breaker
CATALOG NUMBER	BAB2050
UPC	786679302507
PRODUCT LENGTH/DEPTH	3.8 in
PRODUCT HEIGHT	4.8 in
PRODUCT WIDTH	2.2 in
PRODUCT WEIGHT	0.65 lb
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	HACR rated

AMPERAGE RATING	50 A
VOLTAGE RATING	120/240 V
TRIP TYPE	Non-Interchangeable
CIRCUIT BREAKER TYPE	BAB
INTERRUPT RATING	10 kAIC
NUMBER OF POLES	Two-pole
QUANTITY	7
TYPE	Quicklag industrial thermal-magnetic circuit breaker
SPECIAL FEATURES	Bolt-on mounting

[Eaton Specification Sheet - BAB2050](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

