

Eaton BAO100

Eaton Bussmann series low voltage british standard fuse, 100A, AC 500 V, V88/A3, 21 x 87 mm, gL/gG

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	BAO100
PRODUCT LENGTH/DEPTH	87 mm
PRODUCT HEIGHT	22.3 mm
PRODUCT WIDTH	21 mm
PRODUCT WEIGHT	53.2 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	BS88 IEC 60269 EAC

AMPERAGE RATING	100 A
FITTED WITH:	Offset bolted tags
FUSE SIZE	BS88/A3
CURRENT TYPE	AC
MOUNTING DIMENSION	M5
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	73.5 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	500 V
CLASS	Class gG/gL
FUSE TYPE	BAO
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
CONNECTION	74 mm Fixing Centre
CONSTRUCTION	BS88/A3
CONSTRUCTION SIZE	A3
FUSE SHAPE	Offset bolted tags
VOLTAGE TYPE	AC
SUITABLE FOR	CM63F Camaster fuse holder RS63 Red spot fuse holder
VOLTAGE RATING	500 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

