

## Eaton BK/AGC-12-R

Eaton AGC series Fast-acting fuse 12A, 250 Vac, 32 Vdc (self certified), BK-AGC-12-R

<b>PRODUCT NAME</b>	Eaton Bussmann series AGC 1/4" x 1 1/4" 3AG Fast- acting glass tube fuse
<b>CATALOG NUMBER</b>	BK/AGC-12-R
<b>UPC</b>	051712656191
<b>PRODUCT LENGTH/DEPTH</b>	1.25 in
<b>PRODUCT HEIGHT</b>	0.25 in
<b>PRODUCT WIDTH</b>	0.25 in
<b>PRODUCT WEIGHT</b>	0.004 lb
<b>COMPLIANCES</b>	CE Marked RoHS Compliant

<b>USED WITH</b>	out axial leads
<b>AMPERAGE RATING</b>	12 A
<b>INTERRUPT RATING</b>	1 kAIC at 32 Vac
<b>FUSE INDICATOR</b>	Non-indicating
<b>CONNECTION</b>	Ferrule end x ferrule end
<b>RESPONSE TIME</b>	60 min at 135%, 120 sec at 200%
<b>QUANTITY</b>	100
<b>VOLTAGE RATING</b>	250 Vac, 32 Vdc (self certified)
<b>TYPE</b>	Electronic
<b>APPLICATION</b>	Electronic circuits



:
:
:
:

Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com