



Eaton BP72RT

Tripp Lite series 72V Extended Battery Module (EBM) for SmartOnline UPS Systems, 2U Rack/Tower

□□□□

PRODUCT NAME	Eaton Tripp Lite series SmartOnline extended battery module
CATALOG NUMBER	BP72RT
PRODUCT LENGTH/DEPTH	23.8 in
PRODUCT HEIGHT	3.4 in
PRODUCT WIDTH	17.3 in
PRODUCT WEIGHT	86.4 lb
COMPLIANCES	FCC Compliant CE Marked
CERTIFICATIONS	cTUVus UL 1778

TOPOLOGY	Online/Double-conversion
RACK SIZE	2U
COLOR	Black
RACK MOUNTING KIT	Yes

PACKAGE CONTENTS

- 72V Extended Battery Module
- External battery cable
- Rack-mounting hardware
- Quick start guide

USED WITH

2023 redesign:
SU2200RTXLCD2U,
SU2200RTXLCDN,
SU3000RTXLCD2U,
SU3000RTXLCD2UN,
SUINT2200LCD2U,
SUINT3000LCD2U

BATTERY REPLACEMENT

EBP-1616

BATTERY TYPE

Valve Regulated Lead Acid (VRLA)

STANDARD FACTORY WARRANTY

- 2-YEAR FACTORY WARRANTY
- - 2 years
- - Parts, electronics and batteries coverage
- - Standard ground shipping
- - Technical support

EXTENDED SERVICE PLANS

- Service Part Number: TL9SW5Y-3000BC
- Parts, electronics and batteries coverage
- Next business day shipping
- Technical support
- Service Part Number: TLWEBN75XX-7000BC
- Onsite parts and labor coverage for 5 years
- Parts, electronics and batteries coverage
- 24x7 onsite labor

	coverage, next-day response • Next-day shipping • Technical support
RELATIVE HUMIDITY	0-96% non-condensing
TEMPERATURE RANGE	32° to 104°F (0° to 40°C)
SYSTEM REQUIREMENTS	Compatible only with 2023 redesign SU2200RTXLCD2U, SU2200RTXLCDN, SU3000RTXLCD2U, SU3000RTXLCD2UN, SUINT2200LCD2U and SUINT3000LCD2U UPS systems
PRODUCT HIGHLIGHTS	2-year limited warranty (U.S. and Canada -- warranties may vary by country) Connects to select expandable Eaton series SmartOnline UPS systems to add critical runtime Daisy-chain connector supports additional battery packs for even longer runtime Includes heavy-gauge battery cabling with high-current 72V DC connectors Contains 2 batteries connected in parallel: 9Ah per battery, 18Ah total at 72V
MAX NUMBER OF BATTERY PACKS	4
BATTERY REPLACEMENT DESCRIPTION	Hot-swappable, user replaceable batteries. EBM requires 2 Replacement Battery Cartridges.
INPUT CORD DETAILS	15.7 in. connector cord
DC VOLTAGE	72
MINIMUM REQUIRED RACK DEPTH	27 in
OPERATING TEMPERATURE	32° to 104°F (0° to 40°C)
OPTIONAL ACCESSORIES	2 post rackmount (RK2PC)

