


Eaton BSF-063G-NH110-B

Eaton Bussmann series Fuse-link, high speed, 63 A, DC 1000 V, NH1, 40 x 53 x 135, gBat, IEC, dual indicator, bolted connection

PRODUCT NAME	Eaton Bussmann series NH battery storage fuse
CATALOG NUMBER	BSF-063G-NH110-B
PRODUCT LENGTH/DEPTH	135 mm
PRODUCT HEIGHT	53 mm
PRODUCT WIDTH	40 mm
PRODUCT WEIGHT	407 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269-7

AMPERAGE RATING	63 A
BREAKING CAPACITY	100 kA
FUSE INDICATOR	Combination fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	gBat (battery protection)
VOLTAGE TYPE	DC
FUSE SIZE	NH1
RATED VOLTAGE DC	1000 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	111 mm
CURRENT TYPE	DC
MOUNTING DIMENSION	M8
CLASS	Class gBat
CLEARING (I2T)	4300
WATT LOSSES	5 W
PRE ARC (I2T)	470
COLOR	White
INTERRUPT RATING	100 kAIC
FITTED WITH:	Bolted blade
CONNECTION	Bolted blade end x bolted blade end
CONSTRUCTION SIZE	Other
MATERIAL	Ceramic
MOUNTING METHOD	Bolted tag
VOLTAGE RATING	1000 Vdc
APPLICATION	Battery storage
FUSE TYPE	BSF-NH-B
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

