



□□□□□

Eaton BXS63

Eaton Bussmann series low voltage british standard fuse, 63A, AC 440 V, 26 x 100 mm, gL/gG

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	BXS63
PRODUCT LENGTH/DEPTH	27 mm
PRODUCT HEIGHT	27 mm
PRODUCT WIDTH	78.5 mm
PRODUCT WEIGHT	64.6 g
COMPLIANCES	CE RoHS
CERTIFICATIONS	BS



Powering Business Worldwide

□□□□	
AMPERAGE RATING	63 A
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	58 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	440 V
CLASS	Class gG/gL
FUSE TYPE	BXS
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
CONNECTION	Bolt-on
CONSTRUCTION SIZE	Other
FUSE SHAPE	Offset bolted tags Cylindrical
VOLTAGE TYPE	AC
VOLTAGE RATING	440 V
TYPE	Fuse
APPLICATION	for SASIL fuse switch
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

□□□□:	
□□□□:	
□□□:	
□□:	

□□
