

## Eaton C10G1

Eaton Bussmann series low voltage 10 x 38 mm cylindrical/ferrule fuse, rated at 500 Volts AC, 1 Amps, 120 kA Breaking capacity, class gG/gL, without indicator, compatible with a CHM Modular fuse holder

PRODUCT NAME	Eaton Bussmann series low voltage cylindrical fuse
CATALOG NUMBER	C10G1
UPC	051712754217
PRODUCT LENGTH/DEPTH	38 mm
PRODUCT HEIGHT	10 mm
PRODUCT WIDTH	10 mm
PRODUCT WEIGHT	8.2 g
COMPLIANCES	CE Marked GoST-R RoHS Compliant
CERTIFICATIONS	IEC 60269

AMPERAGE RATING	1 A
VOLTAGE RATING	500 V
VOLTAGE TYPE	AC
CLASS	Class C gL/gG
BREAKING CAPACITY	120 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz

DECLARATIONS OF CONFORMITY	<a href="#">eaton-low-voltage-cylindrical-fuse-declaration-of-conformity-uk250946en.pdf</a>

BREAKING CAPACITY	120 kA
CLASS	Class C gL/gG

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

