

## Eaton C10M25

Eaton Bussmann series low voltage 10 x 38 mm cylindrical/ferrule fuse, rated at 400 Volts AC, 25 Amps, 120 kA Breaking capacity, class aM, without indicator, compatible with a CHM Modular fuse holder

|                      |                                                    |
|----------------------|----------------------------------------------------|
|                      |                                                    |
| PRODUCT NAME         | Eaton Bussmann series low voltage cylindrical fuse |
| CATALOG NUMBER       | C10M25                                             |
| UPC                  | 051712754620                                       |
| PRODUCT LENGTH/DEPTH | 38 mm                                              |
| PRODUCT HEIGHT       | 10 mm                                              |
| PRODUCT WIDTH        | 10 mm                                              |
| PRODUCT WEIGHT       | 8.2 g                                              |
| COMPLIANCES          | CE Marked<br>GoST-R<br>RoHS Compliant              |
| CERTIFICATIONS       | IEC 60269                                          |

|                        |          |
|------------------------|----------|
|                        |          |
| AMPERAGE RATING        | 25 A     |
| VOLTAGE RATING         | 400 V    |
| VOLTAGE TYPE           | AC       |
| CLASS                  | Class aM |
| BREAKING CAPACITY      | 120 kA   |
| FREQUENCY RATING - MAX | 62 Hz    |
| FREQUENCY RATING - MIN | 45 Hz    |



|                   |          |
|-------------------|----------|
|                   |          |
| BREAKING CAPACITY | 120 kA   |
| CLASS             | Class aM |

|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
| :               |



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com  
© 2025

Follow us on social media to get the latest product and support information.

