

## Eaton C14G12S

Eaton Bussmann series low voltage 14 x 51 mm cylindrical/ferrule fuse, rated at 500 Volts AC, 12 Amps, 120 kA Breaking capacity, class gG/gL, with striker, compatible with a CH14 Modular fuse holder

|                             |                                                    |
|-----------------------------|----------------------------------------------------|
|                             |                                                    |
| <b>PRODUCT NAME</b>         | Eaton Bussmann series low voltage cylindrical fuse |
| <b>CATALOG NUMBER</b>       | C14G12S                                            |
| <b>PRODUCT LENGTH/DEPTH</b> | 51 mm                                              |
| <b>PRODUCT HEIGHT</b>       | 14 mm                                              |
| <b>PRODUCT WIDTH</b>        | 14 mm                                              |
| <b>PRODUCT WEIGHT</b>       | 20.3 g                                             |
| <b>COMPLIANCES</b>          | RoHS Compliant<br>CE Marked                        |
| <b>CERTIFICATIONS</b>       | IEC 60269                                          |

|                        |               |
|------------------------|---------------|
|                        |               |
| AMPERAGE RATING        | 12 A          |
| VOLTAGE RATING         | 500 V         |
| VOLTAGE TYPE           | AC            |
| CLASS                  | Class C gL/gG |
| BREAKING CAPACITY      | 120 kA        |
| FREQUENCY RATING - MAX | 62 Hz         |
| FREQUENCY RATING - MIN | 45 Hz         |



|                   |               |
|-------------------|---------------|
|                   |               |
| BREAKING CAPACITY | 120 kA        |
| CLASS             | Class C gL/gG |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

: