



Eaton C14G20

Eaton Bussmann series low voltage 14 x 51 mm cylindrical/ferrule fuse, rated at 690 Volts AC, 20 Amps, 80 kA Breaking capacity, class gG/gL, without indicator, compatible with a CH14 Modular fuse holder

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage cylindrical fuse
CATALOG NUMBER	C14G20
UPC	051712754385
PRODUCT LENGTH/DEPTH	51 mm
PRODUCT HEIGHT	14.3 mm
PRODUCT WIDTH	14.3 mm
PRODUCT WEIGHT	20.3 g
COMPLIANCES	CE Marked GoST-R RoHS Compliant
CERTIFICATIONS	IEC 60269

Technical Data	
AMPERAGE RATING	20 A
VOLTAGE RATING	690 V
VOLTAGE TYPE	AC
CLASS	Class C gL/gG
BREAKING CAPACITY	80 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz

Declarations	
DECLARATIONS OF CONFORMITY	eaton-low-voltage-cylindrical-fuse-declaration-of-conformity-uk250946en.pdf

Safety Data	
BREAKING CAPACITY	80 kA
CLASS	Class C gL/gG

Notes: