

Eaton C14G32S

Eaton Bussmann series low voltage 14 x 51 mm cylindrical/ferrule fuse, rated at 500 Volts AC, 32 Amps, 120 kA Breaking capacity, class gG/gL, with striker, compatible with a CH14 Modular fuse holder

PRODUCT NAME	Eaton Bussmann series low voltage cylindrical fuse
CATALOG NUMBER	C14G32S
UPC	051712668361
PRODUCT LENGTH/DEPTH	51 mm
PRODUCT HEIGHT	14 mm
PRODUCT WIDTH	14 mm
PRODUCT WEIGHT	19.4 g
COMPLIANCES	RoHS Compliant CE Marked
CERTIFICATIONS	IEC 60269

AMPERAGE RATING	32 A
VOLTAGE RATING	500 V
VOLTAGE TYPE	AC
CLASS	Class C gL/gG
BREAKING CAPACITY	120 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz



BREAKING CAPACITY	120 kA
CLASS	Class C gL/gG

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

