

Eaton C14G50

Eaton Bussmann series low voltage 14 x 51 mm cylindrical/ferrule fuse, rated at 400 Volts AC, 50 Amps, 120 kA Breaking capacity, class gG/gL, without indicator, compatible with a CH14 Modular fuse holder

PRODUCT NAME	Eaton Bussmann series low voltage cylindrical fuse
CATALOG NUMBER	C14G50
UPC	051712754422
PRODUCT LENGTH/DEPTH	51 mm
PRODUCT HEIGHT	14.3 mm
PRODUCT WIDTH	14.3 mm
PRODUCT WEIGHT	20.6 g
COMPLIANCES	CE Marked GoST-R RoHS Compliant
CERTIFICATIONS	IEC 60269

AMPERAGE RATING	50 A
VOLTAGE RATING	400 V
VOLTAGE TYPE	AC
CLASS	Class C gL/gG
BREAKING CAPACITY	120 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz



BREAKING CAPACITY	120 kA
CLASS	Class C gL/gG

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

