

Eaton C14M6S

Eaton Bussmann series low voltage 14 x 51 mm cylindrical/ferrule fuse, rated at 500 Volts AC, 6 Amps, 120 kA Breaking capacity, class aM, with striker, compatible with a CH14 Modular fuse holder

PRODUCT NAME	Eaton Bussmann series low voltage cylindrical fuse
CATALOG NUMBER	C14M6S
UPC	051712666640
PRODUCT LENGTH/DEPTH	51 mm
PRODUCT HEIGHT	14 mm
PRODUCT WIDTH	14 mm
PRODUCT WEIGHT	19.9 g
COMPLIANCES	RoHS Compliant CE Marked
CERTIFICATIONS	IEC 60269

AMPERAGE RATING	6 A
VOLTAGE RATING	500 V
VOLTAGE TYPE	AC
CLASS	Class aM
BREAKING CAPACITY	120 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz

BREAKING CAPACITY	120 kA
CLASS	Class aM

DECLARATIONS OF CONFORMITY	eaton-low-voltage-cylindrical-fuse-declaration-of-conformity-uk250946en.pdf

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

