



Eaton C22G100S

Eaton Bussmann series low voltage 22 x 58 mm cylindrical/ferrule fuse, rated at 500 Volts AC, 100 Amps, 120 kA Breaking capacity, class gG/gL, with striker, compatible with a CH22 Modular fuse holder

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage cylindrical fuse
CATALOG NUMBER	C22G100S
UPC	051712668538
PRODUCT LENGTH/DEPTH	58 mm
PRODUCT HEIGHT	22 mm
PRODUCT WIDTH	22 mm
PRODUCT WEIGHT	56.2 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269

0000	
AMPERAGE RATING	100 A
VOLTAGE RATING	500 V
VOLTAGE TYPE	AC
CLASS	Class C gL/gG
BREAKING CAPACITY	120 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz

00	
DECLARATIONS OF CONFORMITY	eaton-low-voltage-cylindrical-fuse-declaration-of-conformity-uk250946en.pdf

0000000000	
BREAKING CAPACITY	120 kA
CLASS	Class C gL/gG

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
00:



0000
Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

