

Eaton C22G125

Eaton Bussmann series low voltage 22 x 58 mm cylindrical/ferrule fuse, rated at 500 Volts AC, 125 Amps, 120 kA Breaking capacity, class gG/gL, without indicator, compatible with a CH22 Modular fuse holder

PRODUCT NAME	Eaton Bussmann series low voltage cylindrical fuse
CATALOG NUMBER	C22G125
UPC	051712589932
PRODUCT LENGTH/DEPTH	58 mm
PRODUCT HEIGHT	22.2 mm
PRODUCT WIDTH	22.2 mm
PRODUCT WEIGHT	55.9 g
COMPLIANCES	CE Marked GoST-R RoHS Compliant
CERTIFICATIONS	IEC 60269

AMPERAGE RATING	125 A
VOLTAGE RATING	500 V
VOLTAGE TYPE	AC
CLASS	Class C gL/gG
BREAKING CAPACITY	120 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz



BREAKING CAPACITY	120 kA
CLASS	Class C gL/gG

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

