

Eaton C22G50S

Eaton Bussmann series low voltage 22 x 58 mm cylindrical/ferrule fuse, rated at 690 Volts AC, 50 Amps, 80 kA Breaking capacity, class gG/gL, with striker, compatible with a CH22 Modular fuse holder

PRODUCT NAME	Eaton Bussmann series low voltage cylindrical fuse
CATALOG NUMBER	C22G50S
UPC	051712668507
PRODUCT LENGTH/DEPTH	58 mm
PRODUCT HEIGHT	22 mm
PRODUCT WIDTH	22 mm
PRODUCT WEIGHT	55.3 g
COMPLIANCES	RoHS Compliant CE Marked
CERTIFICATIONS	IEC 60269

AMPERAGE RATING	50 A
VOLTAGE RATING	690 V
VOLTAGE TYPE	AC
CLASS	Class C gL/gG
BREAKING CAPACITY	80 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz

DECLARATIONS OF CONFORMITY	eaton-low-voltage-cylindrical-fuse-declaration-of-conformity-uk250946en.pdf

BREAKING CAPACITY	80 kA
CLASS	Class C gL/gG

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

