



## Eaton C22M100S

Eaton Bussmann series low voltage 22 x 58 mm cylindrical/ferrule fuse, rated at 500 Volts AC, 100 Amps, 120 kA Breaking capacity, class aM, with striker, compatible with a CH22 Modular fuse holder

### □□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series low voltage cylindrical fuse
<b>CATALOG NUMBER</b>	C22M100S
<b>UPC</b>	051712666879
<b>PRODUCT LENGTH/DEPTH</b>	22 mm
<b>PRODUCT HEIGHT</b>	22 mm
<b>PRODUCT WIDTH</b>	58 mm
<b>PRODUCT WEIGHT</b>	55.9 g
<b>COMPLIANCES</b>	RoHS Compliant CE Marked
<b>CERTIFICATIONS</b>	IEC 60269

0000	
AMPERAGE RATING	100 A
VOLTAGE RATING	500 V
VOLTAGE TYPE	AC
CLASS	Class aM
BREAKING CAPACITY	120 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz

00	
DECLARATIONS OF CONFORMITY	<a href="#">eaton-low-voltage-cylindrical-fuse-declaration-of-conformity-uk250946en.pdf</a>

0000000000	
BREAKING CAPACITY	120 kA
CLASS	Class aM

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
00:



0000  
Eaton House  
30 Pembroke Road  
Dublin 4, 0000  
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

