

Eaton C22M125S

Eaton Bussmann series low voltage 22 x 58 mm cylindrical/ferrule fuse, rated at 400 Volts AC, 125 Amps, 120 kA Breaking capacity, class aM, with striker, compatible with a CH22 Modular fuse holder

PRODUCT NAME	Eaton Bussmann series low voltage cylindrical fuse
CATALOG NUMBER	C22M125S
UPC	051712666886
PRODUCT LENGTH/DEPTH	58 mm
PRODUCT HEIGHT	22 mm
PRODUCT WIDTH	22 mm
PRODUCT WEIGHT	54.8 g
COMPLIANCES	RoHS Compliant CE Marked
CERTIFICATIONS	IEC 60269 EAC

AMPERAGE RATING	125 A
VOLTAGE RATING	400 V
VOLTAGE TYPE	AC
CLASS	Class aM
BREAKING CAPACITY	120 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz



BREAKING CAPACITY	120 kA
CLASS	Class aM

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

