

Eaton C22M8

Eaton Bussmann series low voltage 22 x 58 mm cylindrical/ferrule fuse, rated at 690 Volts AC, 8 Amps, 80 kA Breaking capacity, class aM, without indicator, compatible with a CH22 Modular fuse holder

PRODUCT NAME	Eaton Bussmann series low voltage cylindrical fuse
CATALOG NUMBER	C22M8
UPC	051712667432
PRODUCT LENGTH/DEPTH	117 mm
PRODUCT HEIGHT	22 mm
PRODUCT WIDTH	111 mm
PRODUCT WEIGHT	54 g
COMPLIANCES	RoHS Compliant CE Marked
CERTIFICATIONS	IEC 60269

AMPERAGE RATING	8 A
VOLTAGE RATING	690 V
VOLTAGE TYPE	AC
CLASS	Class aM
BREAKING CAPACITY	80 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz



BREAKING CAPACITY	80 kA
CLASS	Class aM

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

