



Eaton C401NWH

Eaton Moeller series Luxury finish range (COPA) - Wiring Devices. Switch, 20A, 2p, neon, white interior, c/w white cover

□□□□

PRODUCT NAME	Eaton Moeller series Luxury finish range (COPA) - Wiring devices
CATALOG NUMBER	C401NWH
PRODUCT LENGTH/DEPTH	40 mm
PRODUCT HEIGHT	86 mm
PRODUCT WIDTH	86 mm
PRODUCT WEIGHT	0.088 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC 60669-1 BS EN 60669-1



Powering Business Worldwide

□□□□

FEATURES	Halogen free Push button switch
SURFACE FINISHING	Matt
SPECIAL FEATURES	Zinc Coated Steel with clear Passivation
TYPE	Copa Switches
AMPERAGE RATING	20 AX
VOLTAGE RATING	250 V AC
CONTACT MATERIAL	Silver Nickel
HEAD STYLE	Combination head
ILLUMINATION	Yes
SURFACE PROTECTION	Untreated
MATERIAL QUALITY	Duroplast
ASSEMBLY ARRANGEMENT	Basic element with full cover plate
BASE COLOR	Gray
BASE MATERIAL	Thermoplastic
TERMINAL MATERIAL	Brass
BUILT-IN DEPTH	25 mm
BUILT-IN INSTALLATION BOX DEPTH - MIN	25 mm
NOMINAL VOLTAGE - MAX	240 V
NUMBER OF MODULES (MODULE SYSTEM)	0
NUMBER OF ROCKERS	1
SWITCH TYPE	Double pole
MOUNTING METHOD	Flush mounted (plaster)
COPA INTERIOR	White insert
DEGREE OF PROTECTION	IP20 IP3X
FASTENING TYPE	Screw mounting
NUMBER OF GANGS	1
FIXING CENTERS	60.3 mm
FRONT PLATE COLOR/FINISHING	White
MATERIAL	Urea Plastic
FRONT PLATE DEPTH	6.5 mm
FRONT PLATE MATERIAL	Thermoplastic
FRONT PLATE/MODULE DIMENSIONS	87 mm x 87 mm
WIRING SYSTEM	2-pole switch

□□

□□□□	eaton-us-power-defense-flyer-br013004en-en-us.pdf
□□□□	eaton-circuit-breakers-bzm-catalog-w1230-7594-gb-int.pdf

METHOD OF OPERATION	Rocker/button
FUNCTION LIGHTING	Illuminated (on)
ROCKER COLOR	White
COLOR	White
TERMINAL CAPACITY (LN AND E)	L + N = 2.5 mm ² (4x) or 4 mm ² (2x) or 6 mm ² (1x) E = 2.5 mm ² (3x) or 4 mm ² (1x) or 6 mm ² (1x)
CONNECTION TYPE	Screw terminal
LABEL SPACE/INFORMATION SURFACE	No
LIGHTING TYPE	Not included
RAL-NUMBER (AKIN)	0
RECOMMENDED BACK BOX DEPTH - MIN	25 mm
SWITCHING CURRENT OF FLUORESCENT LAMPS	20 Ampere AC/DC

□□□□:
□□□□:
□□□:
□□:



□□□□ Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

