



□□□□

Eaton CAP451302

Eaton Crouse-Hinds series Capri UNICAP cable gland, 6-12 cable range, Non-armoured, Polyamide, Industrial, PG 13

□□□□

PRODUCT NAME	Eaton's Crouse-Hinds series Capri UNICAP cable gland
CATALOG NUMBER	CAP451302
PRODUCT LENGTH/DEPTH	27 mm
PRODUCT HEIGHT	40.4 mm
PRODUCT WIDTH	27 mm
PRODUCT WEIGHT	9.6 g



Powering Business Worldwide

□□□□

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	IEC NEC/CEC
INGRESS PROTECTION (IP) RATINGS	IP66
MATERIAL	Polyamide
CABLE RANGE (MIN/MAX)	6-12
GLAND TYPE	Non-armoured
PROTECTION TYPE	Industrial
THREAD SIZE	PG 13
NOMINAL THREAD SIZE METRIC/PG	13
PITCH THREAD	1.411 mm
THREAD LENGTH	9 mm
WRENCH WIDTH	24 mm
HEXAGON ANGULAR DIMENSION	26.4 mm
SUITABLE FOR CABLE DIAMETER - MAX	12 mm
SUITABLE FOR CABLE DIAMETER - MIN	6 mm
MATERIAL QUALITY	Polyamide (PA)
SURFACE PROTECTION	Untreated
DEGREE OF PROTECTION (IP)	IP68
MODEL	Straight
TYPE OF SEALING	Sealing ring
WORKING TEMPERATURE - MAX	100 °C
WORKING TEMPERATURE - MIN	-40 °C
FOR EX-ZONE GAS	None
FOR EX-ZONE DUST	None
FITTED WITH:	Separable Screw Gland Strain Relief
THREAD TYPE	PG
PROTECTION, PROOFING AND RESISTANCE	Shock Resistant

□□

PEP ECO-PASSPORT	eaton-cable-glands-pep-eato-00062-v0101-en.pdf
□□□□	Cable management solutions for OEMs
	UL Unicap QCR V2 Certificate
□□□□	DNV Management System Certificate
	UL Unicap QCRV8 Certificate

