

Eaton CEO100M125

Eaton Bussmann series low voltage British standard fuse, Fuse-link, LV, 100 A, AC 415 V, BS88/A4, 27 x 110 mm, gM, BS, 100M125

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	CEO100M125
UPC	051712839426
PRODUCT LENGTH/DEPTH	111 mm
PRODUCT HEIGHT	28 mm
PRODUCT WIDTH	28 mm
PRODUCT WEIGHT	102.4 g
COMPLIANCES	Contact Manufacturer

AMPERAGE RATING	125 A
FITTED WITH:	Offset bolted tags
FUSE SIZE	BS88/A4
CURRENT TYPE	AC
MOUNTING DIMENSION	M8
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	93.5 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
MOTOR CURRENT RATING	100M125
RATED VOLTAGE AC	415 V
CLASS	Class gM
FUSE TYPE	CEO
UTILIZATION CATEGORY	gM (motor protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	6.5 W
CONNECTION	94 mm fixing centre
CONSTRUCTION	BS88/A4
CONSTRUCTION SIZE	A4
FUSE SHAPE	Offset bolted tags
VOLTAGE TYPE	AC
SUITABLE FOR	RS100 Red spot fuse holder
VOLTAGE RATING	415 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-standard-fuse-declaration-of-conformity-uk250978en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

