

# Eaton CEO100M160

Eaton Bussmann series low voltage british standard fuse, 100A, AC 415 V, V88/A4, 27 x 110 mm, gM, 100M160

|                         |   |
|-------------------------|---|
|                         |   |
| PRODUCT NAME            | Eaton Bussmann series<br>low voltage british<br>standard fuse |
| CATALOG NUMBER          | CEO100M160  |
| UPC                     | 051712839433  |
| PRODUCT<br>LENGTH/DEPTH | 111 mm  |
| PRODUCT HEIGHT          | 28 mm   |
| PRODUCT WIDTH           | 28 mm   |
| PRODUCT WEIGHT          | 102.5 g   |
| COMPLIANCES             | Contact Manufacturer  |

|   |                                 |
|---|---------------------------------|
|   |                                 |
| <b>AMPERAGE RATING</b>                                  | 160 A                           |
| <b>FITTED WITH:</b>                                     | Offset bolted tags              |
| <b>FUSE SIZE</b>  | BS88/A4                         |
| <b>CURRENT TYPE</b>                                     | AC                              |
| <b>MOUNTING DIMENSION</b>                               | M8                              |
| <b>CENTER-TO-CENTER<br/>DISTANCE OF<br/>CONNECTIONS</b> | 93.5 mm                         |
| <b>BREAKING CAPACITY</b>                                | 80 kA                           |
| <b>RATED SWITCHING<br/>CAPACITY</b>                     | 80 kA                           |
| <b>MOTOR CURRENT<br/>RATING</b>                         | 100M160                         |
| <b>RATED VOLTAGE AC</b>                                 | 415 V                           |
| <b>CLASS</b>  | Class gM                        |
| <b>FUSE TYPE</b>  | CEO                             |
| <b>UTILIZATION CATEGORY</b>                             | gM (motor protection)           |
| <b>COLOR</b>  | None                            |
| <b>INTERRUPT RATING</b>                                 | 80 kAIC                         |
| <b>FUSE INDICATOR</b>                                   | None                            |
| <b>INSULATED METAL<br/>GRIPPING LUGS (IMGL)</b>         | No                              |
| <b>WATT LOSSES</b>                                      | 5 W                             |
| <b>CONNECTION</b>                                       | 94 mm fixing centre             |
| <b>CONSTRUCTION</b>                                     | BS88/A4                         |
| <b>CONSTRUCTION SIZE</b>                                | A4                              |
| <b>FUSE SHAPE</b>                                       | Offset bolted tags              |
| <b>VOLTAGE TYPE</b>                                     | AC                              |
| <b>SUITABLE FOR</b>                                     | RS100 Red spot fuse holder      |
| <b>VOLTAGE RATING</b>                                   | 415 V                           |
| <b>TYPE</b>   | Fuse                            |
| <b>APPLICATION</b>                                      | general industrial applications |
| <b>FUSE SYSTEM<br/>(ACCORDING TO IEC<br/>60269)</b>     | Fuse system E                   |

## DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-standard-fuse-declaration-of-conformity-uk250978en.pdf](#)

|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
| :               |



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

