

Eaton CEO63

Eaton Bussmann series low voltage british standard fuse, 63A, AC 500 V, V88/A4, 25 x 110 mm, gL/gG

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	CEO63
UPC	051712839488
PRODUCT LENGTH/DEPTH	109.5 mm
PRODUCT HEIGHT	24.5 mm
PRODUCT WIDTH	21 mm
PRODUCT WEIGHT	77.6 g
COMPLIANCES	Contact Manufacturer

AMPERAGE RATING	63 A
FITTED WITH:	Offset bolted tags
FUSE SIZE	BS88/A4
CURRENT TYPE	AC
MOUNTING DIMENSION	M8
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	94 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	500 V
CLASS	Class gG/gL
FUSE TYPE	CEO
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	5.6 W
CONNECTION	94 mm fixing centre
CONSTRUCTION	BS88/A4
CONSTRUCTION SIZE	A4
FUSE SHAPE	Offset bolted tags
VOLTAGE TYPE	AC
SUITABLE FOR	RS100 Red spot fuse holder
VOLTAGE RATING	500 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-
standard-fuse-declaration-
of-conformity-
uk250978en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

