

Eaton CEX-171-12-348-PN

Eaton Crouse-Hinds series Roughneck CEX panel mounted receptacle, 18A, Unarmoured, Male, Silver plated copper contacts, #16 AWG, Crimp, Pin, 12 shell

PRODUCT NAME	Eaton Crouse-Hinds series Roughneck CEX panel mounted receptacle
CATALOG NUMBER	CEX-171-12-348-PN
UPC	662276615564
PRODUCT LENGTH/DEPTH	5.52 in
PRODUCT HEIGHT	2.5 in
PRODUCT WIDTH	2.5 in
PRODUCT WEIGHT	1.5 lb

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	IECEX/ATEX NEC/CEC
CABLE TYPE	Unarmoured
IECEX/ATEX HAZARDOUS RATING	Zone 1
NEMA RATING	6P 4X
INGRESS PROTECTION (IP) RATINGS	IP66 IP68
AMPERAGE RATING	18 A
CONTACT MATERIAL	Silver plated copper
CONTACT TYPE	Pin
CABLE HARDWARE	Panel Mount
CONNECTOR GENDER	Male
CONTACT SIZE	#16 AWG
CONTACT TERMINATION	Crimp
GROMMET CODE	Panel Mount
SHELL SIZE	12

	IF 1683 - Roughneck Hazardous Multi-pin Connector
	Eaton Specification Sheet - CEX-171-12-348-PN
	Roughneck Multi-pin and Single Pole Connectors brochure
	Roughneck Hazardous Area Multi-pin and Single Pole Connectors catalog page

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

