

Eaton CEX173-C220-376PN

Eaton Crouse-Hinds series Roughneck CEX cable mounted square flange receptacle with cable gland, 30A, Eex d gland, Unarmoured, Male, #12 AWG, Crimp, Pin, 23.0 - 34.0 inner sheath, 29.0 - 41.0 outer sheath, 20 shell

PRODUCT NAME	Eaton Crouse-Hinds series Roughneck CEX cable mounted square flange receptacle with cable gland
CATALOG NUMBER	CEX173-C220-376PN
UPC	662276717527
PRODUCT LENGTH/DEPTH	8.71 in
PRODUCT HEIGHT	3 in
PRODUCT WIDTH	3 in
PRODUCT WEIGHT	1.5 lb

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	IECEX/ATEX NEC/CEC
CABLE TYPE	Unarmoured
IECEX/ATEX HAZARDOUS RATING	Zone 1
NEMA RATING	4X 6P
INGRESS PROTECTION (IP) RATINGS	IP66 IP68
AMPERAGE RATING	30A
CONTACT MATERIAL	Silver plated copper
CONTACT TYPE	Pin
CABLE HARDWARE	Eex d Gland
CONNECTOR GENDER	Male
CONTACT SIZE	#12 AWG
CONTACT TERMINATION	Crimp
GROMMET CODE	Panel Mount
INNER SHEATH (MIN/MAX)	23.0 - 34.0
OUTER SHEATH (MIN/MAX)	29.0 - 41.0
SHELL SIZE	20

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:

[IF 1683 - Roughneck Hazardous Multi-pin Connector](#)

[Eaton Specification Sheet - CEX173-C220-376PN](#)

[Roughneck Multi-pin and Single Pole Connectors brochure](#)

[Roughneck Hazardous Area Multi-pin and Single Pole Connectors catalog page](#)



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

