



Eaton CF30001PL

Eaton CF3000 Addressable control panel:
Cooper, Addressable, Control Panels, Large
System, EN54 Systems, 1 Loop, Polish

□□□□

PRODUCT NAME	Eaton CF3000 Addressable control panel
CATALOG NUMBER	CF30001PL
PRODUCT LENGTH/DEPTH	180 mm
PRODUCT HEIGHT	397 mm
PRODUCT WIDTH	497 mm
PRODUCT WEIGHT	16.804 kg
COMPLIANCES	EN



Powering Business Worldwide



MOUNTING METHOD	Surface mounting
NUMBER OF DETECTION GROUPS	96
NUMBER OF OUTPUTS FOR ACOUSTIC SIGNAL GENERATORS	4
NUMBER OF OUTPUTS FOR OPTICAL SIGNAL GENERATORS	4
NUMBER OF DETECTOR ADDRESSES	200
OPERATING VOLTAGE	24 V
NUMBER OF BATTERIES	2
BATTERY VOLTAGE	12 V
BATTERY CAPACITY	12 Ah
CLASS CHANGE CAPABILITY	Yes
CONSTRUCTION MATERIAL BACK ENCLOSURE	Mild steel
CONSTRUCTION MATERIAL FRONT ENCLOSURE	ABS
HUMIDITY (NON CONDENSING) - MAX	75 %
HUMIDITY (NON CONDENSING) - MIN	0 %
INGRESS PROTECTION	IP30
MAIN INPUT SUPPLY	230 Vac, 50 Hz
MAXIMUM NUMBER OF ADDRESSABLE LOOPS	1
OPERATING TEMPERATURE - MAX	40 °C
OPERATING TEMPERATURE - MIN	-5 °C
SYSTEM TOPOLOGY	Addressable
MAXIMUM NETWORK SIZE (NUMBER OF NODES)	126
WEIGHT (WITHOUT BATTERIES)	16.8 kg
TYPE OF DISPLAY	Touchscreen
AUXILIARY FREE OUTPUT	Yes
AUXILIARY RELAYS	Fire/Fault
PRODUCT BRANDING	Eaton Cooper
SUITABLE FOR	Bus Connection

