



## Eaton CF30004GIND

Eaton CF3000 Addressable control panel,  
Addressable, Control Panels, Large System,  
EN54 Systems, 4 Loops, Indian

□□□□

|                             |  |
|-----------------------------|--|
| <b>PRODUCT NAME</b>         | Eaton CF3000 Addressable control panel |
| <b>CATALOG NUMBER</b>       | CF30004GIND                            |
| <b>PRODUCT LENGTH/DEPTH</b> | 180 mm                                 |
| <b>PRODUCT HEIGHT</b>       | 397 mm                                 |
| <b>PRODUCT WIDTH</b>        | 497 mm                                 |
| <b>PRODUCT WEIGHT</b>       | 16.804 kg                              |
| <b>COMPLIANCES</b>          | EN                                     |



*Powering Business Worldwide*



|   |                  |
|---|------------------|
| <b>MOUNTING METHOD</b>                                  | Surface mounting |
| <b>NUMBER OF DETECTION GROUPS</b>                       | 96               |
| <b>NUMBER OF OUTPUTS FOR ACOUSTIC SIGNAL GENERATORS</b> | 4                |
| <b>NUMBER OF OUTPUTS FOR OPTICAL SIGNAL GENERATORS</b>  | 4                |
| <b>NUMBER OF DETECTOR ADDRESSES</b>                     | 200              |
| <b>OPERATING VOLTAGE</b>                                | 24 V             |
| <b>NUMBER OF BATTERIES</b>                              | 2                |
| <b>BATTERY VOLTAGE</b>                                  | 12 V             |
| <b>BATTERY CAPACITY</b>                                 | 12 Ah            |
| <b>CLASS CHANGE CAPABILITY</b>                          | Yes              |
| <b>CONSTRUCTION MATERIAL BACK ENCLOSURE</b>             | Mild steel       |
| <b>CONSTRUCTION MATERIAL FRONT ENCLOSURE</b>            | ABS              |
| <b>HUMIDITY (NON CONDENSING) - MAX</b>                  | 75 %             |
| <b>HUMIDITY (NON CONDENSING) - MIN</b>                  | 0 %              |
| <b>INGRESS PROTECTION</b>                               | IP30             |
| <b>MAIN INPUT SUPPLY</b>                                | 230 Vac, 50 Hz   |
| <b>MAXIMUM NUMBER OF ADDRESSABLE LOOPS</b>              | 4                |
| <b>OPERATING TEMPERATURE - MAX</b>                      | 40 °C            |
| <b>OPERATING TEMPERATURE - MIN</b>                      | -5 °C            |
| <b>SYSTEM TOPOLOGY</b>                                  | Addressable      |
| <b>MAXIMUM NETWORK SIZE (NUMBER OF NODES)</b>           | 126              |
| <b>WEIGHT (WITHOUT BATTERIES)</b>                       | 16.8 kg          |
| <b>TYPE OF DISPLAY</b>                                  | Touchscreen      |
| <b>AUXILIARY FREE OUTPUT</b>                            | Yes              |
| <b>AUXILIARY RELAYS</b>                                 | Fire/Fault       |
| <b>PRODUCT BRANDING</b>                                 | Eaton Cooper     |
| <b>SUITABLE FOR</b>                                     | Bus Connection   |

