



□□□□

Eaton CFS175-1523

Eaton Crouse-Hinds series PowerGard receptacle assembly, 15A, Two-wire, three-pole, Copper-free aluminum, Single-gang, Dead end, 3/4", 125 Vac

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series PowerGard receptacle assembly
CATALOG NUMBER	CFS175-1523
UPC	662276361805
PRODUCT LENGTH/DEPTH	7.25 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	6.25 in
PRODUCT WEIGHT	3.8 lb



Powering Business Worldwide

□□□□

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 1 Class II, Division 1 Class III
NEMA RATING	3 3R
AMPERAGE RATING	15A
VOLTAGE RATING	125 Vac
MATERIAL	Copper-free aluminum
NUMBER OF GANGS	Single-gang
STYLE	Dead end
TRADE SIZE	3/4"
CONFIGURATION	Two-wire, three-pole

□□

□□□□□	IF 1663 - PowerGard Receptacles
□□□□□□□□	Eaton Specification Sheet - CFS175-1523
□□□□	PowerGard Explosionproof NEMA Locking Receptacles brochure
□□□□	PowerGard Explosionproof NEMA Locking Receptacles catalog page
	PowerGard Explosionproof NEMA Locking Receptacles UL certification (PowerGard Receptacles and Back Boxes Classified for use with Crouse-Hinds ENP Plugs)
	PowerGard Explosionproof NEMA Locking Receptacles UL certification (PowerGard Receptacles and Back Boxes Classified for use with Appleton ECP Plugs and EFS Receptacles)
□□□□	PowerGard Explosionproof NEMA Locking Receptacles Canadian certification (Receptacles with Plugs Interlocked with Switches)
	PowerGard Explosionproof NEMA Locking Receptacles Canadian certification (Receptacles with Plugs)
