



□□□□

Eaton CFSC150-20232

Eaton Crouse-Hinds series PowerGard receptacle assembly, 20A, Two-wire, three-pole, Copper-free aluminum, Single-gang, Through feed, 1/2", 250 Vac

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series PowerGard receptacle assembly
CATALOG NUMBER	CFSC150-20232
UPC	662276358737
PRODUCT LENGTH/DEPTH	7.25 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	6.25 in
PRODUCT WEIGHT	3.8 lb



Powering Business Worldwide

□□□□

AREA CLASSIFICATION Hazardous/Classified Locations

STANDARDS TYPE NEC/CEC

NEC HAZARDOUS RATING Class I, Division 1
Class II, Division 1
Class III

NEMA RATING 3
3R

AMPERAGE RATING 20A

VOLTAGE RATING 250 V AC

MATERIAL Copper-free aluminum

NUMBER OF GANGS Single-gang

STYLE Through feed

TRADE SIZE 1/2"

CONFIGURATION Two-wire, three-pole

□□

□□□□□ [IF 1663 - PowerGard Receptacles](#)

□□□□□□□□ [Eaton Specification Sheet - CFSC150-20232](#)

□□□□ [PowerGard Explosionproof NEMA Locking Receptacles brochure](#)

□□□□ [PowerGard Explosionproof NEMA Locking Receptacles catalog page](#)

[PowerGard Explosionproof NEMA Locking Receptacles Canadian certification \(Receptacles with Plugs Interlocked with Switches\)](#)

[PowerGard Explosionproof NEMA Locking Receptacles UL certification \(PowerGard Receptacles and Back Boxes Classified for use with Appleton ECP Plugs and EFS Receptacles\)](#)

□□□□

[PowerGard Explosionproof NEMA Locking Receptacles UL certification \(PowerGard Receptacles and Back Boxes Classified for use with Crouse-Hinds ENP Plugs\)](#)

[PowerGard Explosionproof NEMA Locking Receptacles Canadian certification \(Receptacles with Plugs\)](#)

