

Eaton CG125 1150

Eaton Crouse-Hinds series CG color-coded cord grip, Cable range min/max: 1.05-1.15", Orange, Straight, Steel, 1-1/4"

PRODUCT NAME	Eaton Crouse-Hinds series CG color-coded cord grip
CATALOG NUMBER	CG125 1150
UPC	784564001122
PRODUCT LENGTH/DEPTH	1.94 in
PRODUCT HEIGHT	2.03 in
PRODUCT WIDTH	2.03 in
PRODUCT WEIGHT	0.4 lb

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	4

Product specifications

CONNECTOR TYPE	Straight
MATERIAL	Steel
TRADE SIZE	1-1/4"
COLOR	Orange
CABLE RANGE (MIN/MAX)	1.05-1.15"

3D CAD DRAWING PACKAGE [Eaton Crouse-Hinds CG125 1150 3D drawing](#)

[Eaton Specification Sheet - CG125 1150](#)

[Crouse-Hinds series CG Color-coded Cord Grips catalog page](#)

[CG Color-coded Cord Grips Canadian certification](#)

[CG Color-coded Cord Grips UL certification](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

