



□□□□□

Eaton CGB195 SG

Eaton Crouse-Hinds series CGB cable gland, Cable range min/max: 0.500-0.625", Non-armoured and tray cable, Non-armoured, Steel, General purpose, Sealing gasket and locknut, 1/2" NPT

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series CGB cable gland
CATALOG NUMBER	CGB195 SG
UPC	782274095318
PRODUCT LENGTH/DEPTH	2.02 in
PRODUCT HEIGHT	1.23 in
PRODUCT WIDTH	1.23 in
PRODUCT WEIGHT	0.21 lb



Powering Business Worldwide

Certifications and compliances	
AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	3R 4

Product specifications	
PROTECTION TYPE	General purpose
CABLE TYPE	Non-armoured Tray cable
GLAND TYPE	Non-armoured
THREAD SIZE	1/2"
THREAD TYPE	NPT
CABLE RANGE (MIN/MAX)	0.500-0.625"
MATERIAL	Steel
SPECIAL FEATURES	Sealing gasket and locknut

Links	
IF 1826 - CGB, CGD and CGE Connectors	IF 1826 - CGB, CGD and CGE Connectors
IF 513A - CG Fittings Installation	IF 513A - CG Fittings Installation
Eaton Specification Sheet - CGB195 SG	Eaton Specification Sheet - CGB195 SG
Crouse-Hinds series Tray Cable Glands brochure	Crouse-Hinds series Tray Cable Glands brochure
Crouse-Hinds series CGB, CGD, CGE and CGFP Non-armoured Glands catalog page	Crouse-Hinds series CGB, CGD, CGE and CGFP Non-armoured Glands catalog page
CGB, CGD, CGE and CGFP Non-armoured Glands UL certification (Cover)	CGB, CGD, CGE and CGFP Non-armoured Glands UL certification (Cover)
CGB, CGD, CGE and CGFP Non-armoured Glands UL certification	CGB, CGD, CGE and CGFP Non-armoured Glands UL certification

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:

