


Eaton CH143DIU

Fuse accessory, Fuse-holder, low voltage, 50 A, AC 690 V, 14 x 51 mm, 3P, IEC, with indicator, replaced by CH143BI, C14G fuses, C14M fuses, IEC 60269-1

PRODUCT NAME	Eaton Bussmann series low voltage cylindrical fuse holder
CATALOG NUMBER	CH143DIU
UPC	051712685177
PRODUCT LENGTH/DEPTH	76 mm
PRODUCT HEIGHT	92 mm
PRODUCT WIDTH	80 mm
PRODUCT WEIGHT	263 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269-2 EAC IEC 60269-1 UL Listed File E14853

USED WITH	C14G, C14M, FW-A14F fuses
AMPERAGE RATING	50 A
NUMBER OF POLES	Three-pole
WIDTH IN NUMBER OF MODULAR SPACINGS	4.5
BUILT-IN DEPTH	51.5 mm
FITTED WITH:	Neon indicator
FUSE SIZE	14 x 51 mm
OPERATING TEMPERATURE DETAILS	-20°C to +70°C
VOLTAGE RATING AT AC	690 V a.c. (IEC) and 700 V a.c. (UL)
VOLTAGE RATING AT DC	750 V d.c. (IEC)
FUSE TYPE	C14G C14M
LOCKABLE	Yes
ACCESSORIES	JV-L Multipole connector kit, CH14-CTP IP20 Protection accessory
TORQUE RATING	Max 3.5 Nm
CONCURRENTLY SWITCHING N-NEUTRAL	No
MATERIAL	Polyester
OPTICAL DEFECT INDICATION	Yes
MOUNTING METHOD	DIN rail 2 x M4 Panel mounting screws
DEGREE OF PROTECTION	IP20
VOLTAGE RATING	690 V
TYPE	fuse accessory
APPLICATION	Industrial and Commercial applications
MODEL	CH14



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

