



Eaton CH223DIU

Eaton Bussmann series 3-Pole modular fuse holder, rated at 690 V a.c./1000 V d.c. (IEC), 700 V a.c. (UL) , 125 Amps (IEC), 100 A (UL), fitted with a neon indicator, suitable for 22 x 58 mm Cylindrical fuses

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage cylindrical fuse holder
CATALOG NUMBER	CH223DIU
UPC	051712685405
PRODUCT LENGTH/DEPTH	77 mm
PRODUCT HEIGHT	123 mm
PRODUCT WIDTH	107 mm
PRODUCT WEIGHT	559.5 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269-2 EAC IEC 60269-1 UL Listed File E14853

USED WITH	C22G, C22M, FWP-(amps)A22F fuses
AMPERAGE RATING	125 A
NUMBER OF POLES	Three-pole
WIDTH IN NUMBER OF MODULAR SPACINGS	6
BUILT-IN DEPTH	51.5 mm
FITTED WITH:	Neon indicator
FUSE SIZE	22 x 58 mm
OPERATING TEMPERATURE DETAILS	-20°C to +70°C
VOLTAGE RATING AT AC	690 V a.c. (IEC) and 700 V a.c. (UL)
VOLTAGE RATING AT DC	1000 V d.c. (IEC)
FUSE TYPE	C22G C22M
LOCKABLE	Yes
ACCESSORIES	JV-L Multipole connector kit, CH22-CTP IP20 Protection accessory, CH22-TPS Microswitch to work with CH223D(I)U
TORQUE RATING	Min 4 Nm/ Max 5 Nm
CONCURRENTLY SWITCHING N-NEUTRAL	No
MATERIAL	Polyester
OPTICAL DEFECT INDICATION	Yes
MOUNTING METHOD	DIN rail 2 x M4 Panel mounting screws
DEGREE OF PROTECTION	IP20
VOLTAGE RATING	690 V
TYPE	fuse accessory
APPLICATION	Industrial and Commercial applications
MODEL	CH22

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-cylindrical-fuse-holder-declaration-of-conformity-uk251073en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

