



Eaton CH224DU

Fuse accessory, Fuse-holder, low voltage, 125 A, AC 690 V, 22 x 58 mm, 4P, IEC, UL, C22M and C22G fuses, IEC 60269-1, IEC 60269-2, IP20

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage cylindrical fuse holder
CATALOG NUMBER	CH224DU
UPC	051712685047
PRODUCT LENGTH/DEPTH	77 mm
PRODUCT HEIGHT	123 mm
PRODUCT WIDTH	142 mm
PRODUCT WEIGHT	632 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269-2 EAC IEC 60269-1 UL Listed File E14853

□□□□

USED WITH	C22G, C22M, FWP-(amps)A22F fuses
AMPERAGE RATING	125 A
NUMBER OF POLES	Four-pole
WIDTH IN NUMBER OF MODULAR SPACINGS	8
BUILT-IN DEPTH	51.5 mm
FUSE SIZE	22 x 58 mm
OPERATING TEMPERATURE DETAILS	-20°C to +70°C
VOLTAGE RATING AT AC	690 V a.c. (IEC) and 700 V a.c. (UL)
VOLTAGE RATING AT DC	1000 V d.c. (IEC)
FUSE TYPE	C22G C22M
LOCKABLE	Yes
ACCESSORIES	JV-L Multipole connector kit, CH22-CTP IP20 Protection accessory
TORQUE RATING	Min 4 Nm/ Max 5 Nm
CONCURRENTLY SWITCHING N-NEUTRAL	No
MATERIAL	Polyester
OPTICAL DEFECT INDICATION	No
MOUNTING METHOD	DIN rail 2 x M4 Panel mounting screws
DEGREE OF PROTECTION	IP20
VOLTAGE RATING	690 V
TYPE	fuse accessory
APPLICATION	Industrial and Commercial applications
MODEL	CH22

□□

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-cylindrical-fuse-holder-declaration-of-conformity-uk251073en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

