



□□□□

Eaton CHFQ115

Eaton 3/4" Thermal magnetic circuit breakers, 15 A,10 kAIC,Single-pole,120/240V, #14-8, (2) #14-10 AWG Cu/Al,Type CH Loadcenters, Type CHFQ 3/4-Inch,

□□□□

PRODUCT NAME	Eaton Classified 3/4" thermal magnetic circuit breaker
CATALOG NUMBER	CHFQ115
UPC	629113000075
PRODUCT LENGTH/DEPTH	7.25 in
PRODUCT HEIGHT	6.5 in
PRODUCT WIDTH	4.48 in
PRODUCT WEIGHT	1.96 lb
CERTIFICATIONS	UL 489
CATALOG NOTES	Replacement for Square D Type QO Breakers. Requires one 3/4-inch (19.1 mm) space.



Powering Business Worldwide

