



□□□□

## Eaton CHFQ130

Eaton 3/4" Thermal magnetic circuit breakers, Type CHFQ 3/4-Inch, 120/240V, #14-8, (2) #14-10 AWG Cu/Al, Type CH Loadcenters, 30 A, 10 kAIC, Single-pole

□□□□

<b>PRODUCT NAME</b>	Eaton Classified 3/4" thermal magnetic circuit breaker
<b>CATALOG NUMBER</b>	CHFQ130
<b>UPC</b>	629113000105
<b>PRODUCT LENGTH/DEPTH</b>	7.25 in
<b>PRODUCT HEIGHT</b>	6.5 in
<b>PRODUCT WIDTH</b>	4.48 in
<b>PRODUCT WEIGHT</b>	1.96 lb
<b>CERTIFICATIONS</b>	UL 489
<b>CATALOG NOTES</b>	Replacement for Square D Type QO Breakers. Requires one 3/4-inch (19.1 mm) space.



Powering Business Worldwide

