



□□□□

Eaton CHFQ230CS

Eaton 3/4" Thermal magnetic circuit breakers, Type CHFQ 3/4-Inch, 30 A, 10 kAIC, Two-pole, 120/240V, #14-8, (2) #14-10 AWG Cu/Al, Type CH Loadcenters

□□□□

PRODUCT NAME	Eaton Classified 3/4" thermal magnetic circuit breaker
CATALOG NUMBER	CHFQ230CS
UPC	629113000211
PRODUCT LENGTH/DEPTH	7.25 in
PRODUCT HEIGHT	6.5 in
PRODUCT WIDTH	4.48 in
PRODUCT WEIGHT	1.96 lb
CERTIFICATIONS	UL 489
CATALOG NOTES	Replacement for Square D Type QO Breakers. Requires two 3/4-inch (19.1 mm) spaces.



Powering Business Worldwide

