

Eaton CHM3DNIU

Eaton Bussmann series CHM modular fuse holder, 600V (UL), 690V (IEC), 30A (UL), 32A (IEC), 200 kAIC, Modular fuse holder, Three-pole - CHM3DNIU

PRODUCT NAME	Eaton Bussmann series CHM modular fuse holder
CATALOG NUMBER	CHM3DNIU
UPC	051712362795
PRODUCT LENGTH/DEPTH	0.001 mm
PRODUCT HEIGHT	0.001 mm
PRODUCT WIDTH	0.001 mm
PRODUCT WEIGHT	221 g
COMPLIANCES	Contact factory RoHS Compliant

USED WITH	For use with CHM 10 mm X 38 mm fuse and Midget fuse
AMPERAGE RATING	30A (UL), 32A (IEC)
NUMBER OF POLES	Three-pole
OPERATING TEMPERATURE - MAX	90 °C
OPERATING TEMPERATURE - MIN	-20 °C
INTERRUPT RATING	200 kAIC
WIRE SIZE	#18-4 AWG
QUANTITY	3
VOLTAGE RATING	600 V (UL), 690 V (IEC)
TYPE	Modular fuse holder

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

