



## Eaton CM100CF

Fuse accessory, Fuse-holder, low voltage, 100 A, AC 690 V, HRCII-MISC, 1P, CSA, black, 35 mm DIN-Rail or single screw mounting, CSA C22.2 NO.39

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series low voltage british standard fuse holder
<b>CATALOG NUMBER</b>	CM100CF
<b>UPC</b>	051712551427
<b>PRODUCT LENGTH/DEPTH</b>	60 mm
<b>PRODUCT HEIGHT</b>	125 mm
<b>PRODUCT WIDTH</b>	35.6 mm
<b>PRODUCT WEIGHT</b>	218.8 g
<b>COMPLIANCES</b>	Contact factory

□□□□	
AMPERAGE RATING	100 A
CONNECTION TYPE	Screwed terminal
FEATURES	Halogen free
NUMBER OF POLES	Single-pole
VOLTAGE RATING AT AC	690 V a.c.
ACCESSORIES	63-100BS, 63-100CML, 63-100LSC, NI
COLOR	Black
BUS-MOUNTING TYPE	Yes
CONSTRUCTION SIZE	Other
MOUNTING METHOD	DIN rail Bolted panel
VOLTAGE RATING	690 V
TYPE	fuse accessory
SPECIAL FEATURES	2/3 Pole ganging, Unique cable termination, Neon indicator, Dual mounting capability
APPLICATION	general industrial applications
MODEL	Camaster

□□

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
□□:



□□□□  
Eaton House  
30 Pembroke Road  
Dublin 4, □□□  
Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the latest product and support information.

