

## Eaton CM20FW

Fuse accessory, Fuse-holder, low voltage, 20 A, AC 660 V, BS88, 1P, BS, white, fuse-link NITD

<b>PRODUCT NAME</b>	Eaton Bussmann series low voltage british standard fuse holder
<b>CATALOG NUMBER</b>	CM20FW
<b>PRODUCT LENGTH/DEPTH</b>	60 mm
<b>PRODUCT HEIGHT</b>	94 mm
<b>PRODUCT WIDTH</b>	25 mm
<b>PRODUCT WEIGHT</b>	134.5 g
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	IEC 60269

AMPERAGE RATING	20 A
CONNECTION TYPE	Screwed terminal
FEATURES	Halogen free
NUMBER OF POLES	Single-pole
VOLTAGE RATING AT AC	690 V a.c.
FUSE TYPE	NITD NIT
COLOR	White
BUS-MOUNTING TYPE	Yes
CONNECTION	Front Connected
CONSTRUCTION SIZE	Other
MOUNTING METHOD	DIN rail
TYPE	fuse accessory
APPLICATION	general industrial applications
MODEL	Camaster

DECLARATIONS OF CONFORMITY	<a href="#">eaton-low-voltage-british-standard-fuse-holder-declaration-of-conformity-uk251074en.pdf</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com  
  
© 2025

Follow us on social media to get the latest product and support information.

