

## Eaton CM32FC

Fuse accessory, Fuse-holder, low voltage, 32 A, AC 690 V, BS88/A1, 1P, BS, DIN rail or screw mounting, black, fuse-link NITD

<b>PRODUCT NAME</b>	Eaton Bussmann series low voltage british standard fuse holder
<b>CATALOG NUMBER</b>	CM32FC
<b>UPC</b>	051712839549
<b>PRODUCT LENGTH/DEPTH</b>	60 mm
<b>PRODUCT HEIGHT</b>	94 mm
<b>PRODUCT WIDTH</b>	25 mm
<b>PRODUCT WEIGHT</b>	134.3 g
<b>COMPLIANCES</b>	Contact factory

<b>AMPERAGE RATING</b>	32 A
<b>CONNECTION TYPE</b>	Screwed terminal
<b>FEATURES</b>	Halogen free
<b>NUMBER OF POLES</b>	Single-pole
<b>VOLTAGE RATING AT AC</b>	690 V a.c.
<b>FUSE TYPE</b>	NITD NIT
<b>ACCESSORIES</b>	32BSC, 32CMLC, 32LSCC, NI
<b>COLOR</b>	Black
<b>BUS-MOUNTING TYPE</b>	Yes
<b>CONNECTION</b>	Front Connected
<b>CONSTRUCTION SIZE</b>	Other
<b>MOUNTING METHOD</b>	DIN rail
<b>VOLTAGE RATING</b>	660 V
<b>TYPE</b>	fuse accessory
<b>APPLICATION</b>	general industrial applications
<b>MODEL</b>	Camaster

<b>DECLARATIONS OF CONFORMITY</b>	<a href="#">eaton-low-voltage-british-standard-fuse-holder-declaration-of-conformity-uk251074en.pdf</a>
-----------------------------------	---

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
:

