

Eaton CM32FCG

Fuse accessory, Fuse-holder, low voltage, 32 A, AC 690 V, BS88/A1, 1P, BS, DIN rail or screw mounting, green, fuse-link NITD

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse holder
CATALOG NUMBER	CM32FCG
PRODUCT LENGTH/DEPTH	32 mm
PRODUCT HEIGHT	94 mm
PRODUCT WIDTH	60 mm
PRODUCT WEIGHT	163 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269

AMPERAGE RATING	32 A
CONNECTION TYPE	Screwed terminal
FEATURES	Halogen free
NUMBER OF POLES	Single-pole
VOLTAGE RATING AT AC	690 V a.c.
FUSE TYPE	NITD NIT
ACCESSORIES	32BSC, 32CMLC, 32LSCC, NI
COLOR	Green
BUS-MOUNTING TYPE	Yes
CONNECTION	Front Connected
CONSTRUCTION SIZE	Other
MOUNTING METHOD	DIN rail
TYPE	fuse accessory
APPLICATION	general industrial applications
MODEL	Camaster

DECLARATIONS OF CONFORMITY	eaton-low-voltage-british-standard-fuse-holder-declaration-of-conformity-uk251074en.pdf
-----------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

: